

# CYMEL<sup>®</sup> 370 resin

## PRODUCT DESCRIPTION

CYMEL 370 resin is a partially methylated melamine crosslinker supplied in isobutanol. Like other high imino resins, Cymel 370 is fast reacting and has a high tendency to self-condense resulting in films with high film hardness, gloss, chemical resistance and exterior durability. The high reactivity, combined with high solids content makes CYMEL 370 resin suitable for a wide range of solventborne and waterborne industrial bake formulations.

## BENEFITS

- Fast cure response
- Very high gloss
- Good stability
- Chemical resistance

## APPLICATION AREAS

- General industrial coatings
- Primer formulations
- Water-based coatings

## PHYSICAL PROPERTIES

Property	Range	Method
Appearance	Clear Liquid	Visual
Non-volatile by wt.	86-90%	Foil, 45 min/45°C
Viscosity, 23°C	6000-10500 mPa·s	Dynamic (Cone & Plate)
Free formaldehyde	≤ 3.5%	Sulfite
Color, APHA	≤ 70	ISO 6271

## SOLUBILITY

Alcohols	Complete
Esters	Complete
Ketones	Complete
Aromatic hydrocarbons	Partial
Aliphatic hydrocarbons	Insoluble
Water	Partial

## COMPATIBILITY

Acrylic resins	Very good
Alkyd resins	Very good
Polyester resins	Very good
Epoxy resins	Very good

## BACKBONE POLYMER SELECTION

CYMEL 370 resin contains a combination of methoxymethyl and methylol functionalities, making it a very effective crosslinker for backbone polymer resins containing hydroxyl, carboxyl, and amide functional groups, such as those found on alkyd, polyester or acrylic resins. Although the optimum level of CYMEL 370 resin should be determined experimentally, ratios of 25 to 35% based on resin solids are typically most effective.

## CATALYSIS

CYMEL 370 resin may not require the addition of an acid catalyst to the formulation to obtain effective cure. In many instances, the acidity of the backbone polymer in the formulation is sufficient to catalyze the reaction under normal baking conditions (15-20 minutes at 120-150°C). If catalyst addition is required, then 0.5-1.0% of CYCAT<sup>®</sup> 4040 catalyst or CYCAT 296-9 catalyst based on total resin solids is recommended.

## FORMULATION STABILITY

The stability of solvent-borne systems containing CYMEL 370 resin can be enhanced by the addition of primary alcohols, amines, or a combination of these. Low molecular weight primary alcohols such as ethanol and n-butanol are most effective. Recommended amines are TEA, DMEA or 2-AMP at a concentration of 0.5-1.0% on total binder solids. For best stability in waterborne systems, a pH between 7.5-8.5 should be maintained using tertiary amines only.

## STORAGE STABILITY

CYMEL 370 resin has a shelf life of 3 years from the date of manufacture when stored at temperatures between 5°C and 30°C. Although lower temperatures are not detrimental to stability, its viscosity will increase, possibly making the resin difficult to pump or pour. The viscosity will reduce again on warming, but care should be taken to avoid excessive local heat as this can cause an irreversible increase in viscosity.

---

• Worldwide Contact Info: [www.allnex.com](http://www.allnex.com) •

---

Disclaimer: Allnex Group companies ("Allnex") decline any liability with respect to the use made by anyone of the information contained herein. The information contained herein represents Allnex's best knowledge thereon without constituting any express or implied guarantee or warranty of any kind (including, but not limited to, regarding the accuracy, the completeness or relevance of the data set out herein). Nothing contained herein shall be construed as conferring any license or right under any patent or other intellectual property rights of Allnex or of any third party. The information relating to the products is given for information purposes only. No guarantee or warranty is provided that the product and/or information is adapted for any specific use, performance or result and that product and/or information do not infringe any Allnex and/or third party intellectual property rights. The user should perform its own tests to determine the suitability for a particular purpose. The final choice of use of a product and/or information as well as the investigation of any possible violation of intellectual property rights of Allnex and/or third parties remains the sole responsibility of the user.

Notice: Trademarks indicated with the ®, ™ or \* are registered, unregistered or pending trademarks of Allnex Belgium SA or its directly or indirectly affiliated Allnex Group companies.

February 2015