

# 3M™ Glass Bubbles Floated Product Series

## Introduction

3M™ Glass Bubbles are engineered hollow glass microspheres that are alternatives to conventional fillers and additives such as silicas, calcium carbonate, talc, clay, etc., for many demanding applications. These low-density particles are used in a wide range of industries to reduce part weight, lower costs and enhance product properties.

The spherical shape of 3M glass bubbles offers a number of important benefits, including: higher filler loading, lower viscosity/improved flow, and reduced shrinkage and warpage. It also helps the 3M glass bubbles blend readily into compounds, and makes them adaptable to a variety of production processes, including spraying, casting and molding. In addition, they offer greater survivability under demanding processing conditions, such as injection molding, and also produce stable voids, which results in low thermal conductivity and a low dielectric constant.

The chemically stable soda-lime-borosilicate glass composition of 3M glass bubbles provides excellent water resistance, to create more stable emulsions. They are also non-combustible and non-porous, so they do not absorb resin. And, their low alkalinity gives 3M glass bubbles compatibility with most resins, stable viscosity and long shelf life.

**3M Glass Bubbles Floated Series** offer the same combination of strength and light weight as standard 3M glass bubbles, with an added surface treatment of special coupling agents, for use in high-tech applications such as aerospace and hydrospace syntactic foam, radomes and printed wire boards.

They are available in a variety of sizes and grades for various product and processing requirements.

## Typical Properties (Not for specification purposes)

### Nitrogen Isostatic Crush Strength (3M QCM 14.1.5)

Product	Test Pressure (psi)	Target Fractional Survival	Minimum Fractional Survival
A16/500	500	90%	80%
A20/1000	1,000	90%	80%
H20/1000	1,000	90%	80%
D32/4500	4,500	90%	80%
H50/10,000 EPX*	6,000	90%	90%

\*Per ASTM D3102-78 in glycerol.

### True Density (3M QCM 14.24.6)

Product	Typical	True Density (g/cc)	
		Minimum	Maximum
A16/500	0.16	0.14	0.18
A20/1000	0.20	0.18	0.22
H20/1000	0.20	0.18	0.22
D32/4500	0.32	0.30	0.34
H50/10,000 EPX	0.50	0.48	0.52

### Chemical Resistance

In general, the chemical properties of 3M glass bubbles resemble those of a soda-lime-borosilicate glass.

### Surface Treatment

A16/500, A20/1000 and D32/4500 glass bubbles have methacrylate chromic chloride surface treatment, H20/1000 and H50/10,000 EPX glass bubbles have epoxy silane surface treatment.

### Packing Factor (Ratio of bulk density to true particle density)

Varies from 55% to 68%.

### Oil Absorption

31-36 g oil/100 cc of 3M glass bubbles, per ASTM D1483.

## Typical Properties (Continued)

### Thermal Properties: Conductivity

0.06-0.16 W/m•K at 68°F (20°C), based on theoretical calculations. Conductivity increases with temperature and product density. The thermal conductivity of a composite will depend on the matrix material and volume loading of 3M glass bubbles.

### Thermal Properties: Stability

Appreciable changes in bubble properties may occur above 1112°F (600°C) depending on temperature and duration of exposure.

### Flotation (3M QCM 37.2)

Product	Floater (% by bulk volume) Minimum
A16/500	99%
A20/1000	99%
H20/1000	99%
D32/4500	99%
H50/10,000 EPX	99%

### Volatile Content (3M QCM 1.5.7)

Maximum of 0.5 percent by weight.

### Alkalinity (3M QCM 55.19)

Maximum of 0.3 milliequivalents per gram

### pH

Because 3M™ Glass Bubbles are a dry powder, pH is not defined. The pH effect will be determined by the alkalinity as indicated above. When 3M glass bubbles are mixed with deionized water at 5 volume percent loading, the resulting pH of the slurry is typically 9.1 to 9.9, as measured by a pH meter.

### Dielectric Constant

1.3 to 1.5 @ 100 MHz, based on theoretical calculations. The dielectric constant of a composite will depend on the matrix material and volume loading of 3M glass bubbles.

### Size

Product	Particle Size (microns, by volume) (3M QCM 193.2)			
	Distribution			Effective Top Size
	10th%	50th%	90th%	95th%
A16/500	30	60	95	115
A20/1000	25	60	90	105
H20/1000	25	60	90	105
D32/4500	20	40	65	80
H50/10,000 EPX	15	35	60	70

### Hard Particles (3M QCM 93.4.3)

No hard particles (e.g., glass slag, flow agent, etc.) greater than U.S. number 40 (420 microns) standard sieve will exist.

### Sieve Analysis (3M QCM 93.4.4)

For *A16/500*, *A20/1000*, *H20/1000* glass bubbles: Using a 10 gram sample on a U.S. number 80 standard sieve (177 microns), a maximum of five percent by weight glass bubbles will be retained on the sieve.

For *D32/4500*, *H50/10,000 EPX* glass bubbles: Using a 10 gram sample on a U.S. number 200 sieve (74 microns), a maximum of three percent by weight glass bubbles will be retained on the sieve.

### Appearance (3M QCM 22.85)

White to the unaided eye. *A16/500*, *A20/1000*, and *D3L/4500* have a green tint from the surface treatment.

### Flowability (3M QCM 22.83)

3M glass bubbles remain free flowing for at least one year from the date of manufacture if stored in the original, unopened container in the minimum storage conditions of an unheated warehouse.

### Labeling

3M glass bubbles will be packaged in suitable containers to help prevent damage during normal handling and shipping. Each container will be labeled with:

1. Name of manufacturer
2. Type of 3M glass bubbles
3. Lot number
4. Quantity in pounds

## Storage and Handling

To help ensure ease of storage and handling while maintaining free flowing properties, 3M™ Glass Bubbles have been made from a chemically stable glass and are packaged in a heavy duty polyethylene bag within a cardboard container. Minimum storage conditions should be unopened cartons in an unheated warehouse.

Under high humidity conditions with the ambient temperature cycling over a wide range, moisture can be drawn into the bag as the temperature drops and the air contracts. The result may be moisture condensation within the bag. Extended exposure to these conditions may result in “caking” of the 3M glass bubbles to various degrees. To minimize the potential for “caking” and prolong the storage life, the following suggestions are made:

1. Carefully re-tie open bags after use.
2. If the polyethylene bag is punctured during shipping or handling, use this bag as soon as possible, patch the hole, or insert the contents into an undamaged bag.
3. During hot and humid months, store in the driest, coolest space available.
4. If controlled storage conditions are unavailable, carry a minimum inventory, and process on a first in/first out basis.

Dusting that may occur while handling and processing can be minimized by the following procedures:

1. For eye protection wear chemical safety goggles. For respiratory system protection wear an appropriate NIOSH/MSHA-approved respirator. (For additional information about personal protective equipment, refer to Material Safety Data Sheet.)
2. Use appropriate ventilation in the work area.
3. Pneumatic conveyor systems have been used successfully to transport 3M glass bubbles without dusting from shipping containers to batch mixing equipment. Static eliminators should be used to help prevent static charges.

Diaphragm pumps have been used to successfully convey 3M glass bubbles. Vendors should be consulted for specific recommendations.

3M glass bubble breakage may occur if the product is improperly processed. To minimize breakage, avoid high shear processes such as high-speed Cowles™ Dissolvers, point contact shear such as gear pumps or 3-roll mills, and processing pressures above the strength test pressure for each product.

## Health and Safety Information

For product Health and Safety Information, refer to product label and Material Safety Data Sheet (MSDS) before using product.

## Packaging Information

### Mini-Box

A single corrugated box with a plastic liner.  
Box dimensions are 16 in. × 16 in. × 20 in.

### Small Box (10 Cubic ft.)

A single corrugated box with a plastic liner. All boxes are banded together and to the wooden pallet. 4 boxes per pallet.

Box dimensions are 22 in. × 19 in. × 39 in.  
Pallet size is 42 in. × 48 in.

## Box Weights

Product	Mini-Box	Small Box
A16/500	10 lb.	50 lb.
A20/1000	10 lb.	50 lb.
H20/1000	10 lb.	50 lb.
D32/4500	10 lb.	100 lb.
H50/10,000 EPX	10 lb.	100 lb.

## Additional Information

3M™ Glass Bubbles are supported by global sales, technical and customer service resources, with fully-staffed technical service laboratories in the U.S., Europe, Japan, Latin America and Southeast Asia. Users benefit from 3M's broad technology base and continuing attention to product development, performance, safety and environmental issues.

For additional technical information on 3M glass bubbles in the United States, call 3M Advanced Materials Division, 800-367-8905.

For other 3M global offices, and information on additional 3M products, visit our web site at: [www.3M.com/glassbubbles](http://www.3M.com/glassbubbles)

**Warranty, Limited Remedy, and Disclaimer:** Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. User is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application. User is solely responsible for evaluating third party intellectual property rights and for ensuring that user's use of 3M product does not violate any third party intellectual property rights. Unless a different warranty is specifically stated in the applicable product literature or packaging insert, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OF NON-INFRINGEMENT OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

**Limitation of Liability:** Except where prohibited by law, 3M will not be liable for any loss or damages arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

**Technical Information:** Technical information, recommendations, and other statements contained in this document or provided by 3M personnel are based on tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed. Such information is intended for persons with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.



### Advanced Materials Division 3M Center

St. Paul, MN 55144-1000  
1-800-367-8905  
[www.3M.com/glassbubbles](http://www.3M.com/glassbubbles)

Please recycle. Printed in USA.  
Issued: 6/15 © 3M 2015.  
All rights reserved. 10780HB  
98-0212-4117-3 Rev. B

COWLES is a trademark of MorehouseCowles.  
3M is a trademark of 3M Company. Used under  
license by 3M subsidiaries and affiliates.