

烟台优联新材料有限公司 YANTAI YOLIAN ADVANCED MATERIALS CO.,LTD

Add:#406 Juzheng Building,No. 44 Zhujiang RD,Economic and Technological Development Dist.,Yantai China Tel&Fax:0086-535-6393167 Email:export@modularresins.com Website: www.modularresins.com

# **Indoor Chemical Matt Hardener**

# YL-68

## (Equivalent to Vestgon B68)

## 1.Description:

Matting hardner M68 is a composed salt of cyclic-amidine and multi-acid. When the double curing group in the molecular structure is cross-linked with the epoxy resin, the different curing rates generate uneven shrinkage, thus forming a flat and dense matte coating film.

## 2.Specification:

Appearance	Fine white powder			
Purity	≧90%			
Melting range	200-230°C			

## 3.Application:

It is used for pure epoxy resin, epoxy\polyester hybrid powder coatings to achieve matting surface with excellent mechanic quality and wonderful appearance.

## 4.Reference formulation:

Gloss 60°(%)	5-6	20	40	70
Epoxy resin(E-12)	54.5	39.7	35.7	31.8
Polyester (acidity:25-35mgKOH/g)	/	14.8	20.8	26.7



### 烟台优联新材料有限公司

### YANTAI YOLIAN ADVANCED MATERIALS CO., LTD

Add:#406 Juzheng Building,No. 44 Zhujiang RD,Economic and Technological Development Dist.,Yantai China Tel&Fax:0086-535-6393167 Email:export@modularresins.com Website: www.modularresins.com

YL-68	5.0	5.0	3.0	1.0
Filler(BaSo4, CaCo3)	40	40	40	40
Leveling agent(H-8588)	0.5	0.5	0.5	0.5
Carbon black	0.5-1	0.5-1	0.5-1	0.5-1

Curing condition: 180°C 20-25 minutes /190°C 10-12 minutes / 200°C 8-10minutes

### 5.Notice:

YL-68 Matt hardener's compatibility with resin isn't well for its high melting point, then it's necessary to disperse YL-68 with other materials well or to make the curing temperature higher( $\geq 100^{\circ}$ C), or extrude for some more times to avoid of it. Because YL-68 is easy to be yellowing in white powder coating, then use it with care or use the physical matting agent supplied by our company in high whiteness powder coating.

#### 6.Package & Storage:

(1). Package: 20kgs/ Kraft paper bag lined with polyethylene bag.

(2). Store in a cool and dry place to avoid contacting other chemical products. Seal tightly after

using. As this product is irritant to respiratory tract, please wear dustproof mask and glove when

operating.

(3). Validity will be 1 years under normal temperature.